



PRODUCT DESCRIPTION

iForm 65A Flexible(TPU-like)Resin

YOUSU iForm 65A resin fit for Medical devices and anatomical models. It is a type of UV-cured 3D printing resin that mimics the properties of rubber. Polishing with TPM is Better. Using TPM, wash your printed parts within 1-2 minutes. Use longer wash times if necessary.

ATTRIBUTES		
Resin model	iForm 65A Flexible(TPU-like) resin for LCD	
Grade	iForm 65A	
Color	black	
Viscosity(25℃)	130-150cps	
Wavelength	405nm	
MECHANICAL PROPERTIES		
Tensile strength	3.6-4.2MPa	ASTM D638
Elongation at break	235-295%	ASTM D638
Notched impact strength	15-20J/m	ASTM D256
Heat deflection temperature(0.45MPa)	/℃	ASTM D648
Hardness	65-75D	ASTM D2240
PRINTING IMFORMATION		
	Color Screen	Mono Screen
Normal exposure time	8s	2-2.5s
Bottom exposure time	60s	20-25s
Bottom layer	6	3
Layer thickness	0.05mm	

POST-PROCESSING STEP

1. Once the dental model is completed, model need to rinse in water and dry normally.
2. Post-curing is required for this resin to reach its high surface hardness and scratch resistance.

Any technical information provided and recommendations made herein are intended to assist customers in determining whether our products are suitable for your applications. We request that you must test our products before use and accepted at your own risk. Neither Yousu nor its affiliates shall be responsible for the use of this information, or of any product, method or apparatus mentioned, and you must make your own determination of its suitability and completeness for your own use, for the protection of the environment, and for the health and safety of your employees and purchasers of your products. We do not guarantee results, freedom from patent infringement, or suitability of resultant products for any suggested application with respect to the use of any formula or material described herein.